

Our Commitment to You

We stand behind the quality of our products by offering a factory-backed Extended Warranty Program. Your purchase is a long-term investment, and you can count on our Extended Warranty Program to protect your investment.



Extended Warranty at a Glance

- Lower risk of unexpected failure costs beyond factory standard warranty
- Minimized downtime with repairs completed by factory-trained technicians using genuine Cummins parts
- No deductibles or hidden charges
- Up to 10 years extended warranty coverage with fixed-price contract
- Variety of coverage terms and options to meet your needs
- Extended warranty coverage is fully transferable
- Protection against rising parts, labor and travel costs
- Backed by nearly 100 years of experience through Cummins
- Supported by global network of authorized Cummins service providers
- World-class Cummins factory technical assistance

Extended Warranty Overview

When to Buy

- At time of generator purchase
- or -
- Before base warranty expires, during comprehensive coverage period

Where to Buy

- Your local distributor or dealer. Locate a Dealer at homegenerators.cummins.com

What's Included

- Repair of all failures resulting from defects in material, design or workmanship
- Standard base warranty coverage (until extended warranty coverage starts)
- Choice of coverage level
- Immediate benefit of coverage

What's Excluded

- Scheduled maintenance
- Repair of failures that result from customer abuse, neglect or misuse
- Product failures related to improper application, installation, storage or maintenance

These conditions are subject to change. Please contact your distributor or dealer for terms and conditions specific to your product.



Cummins Inc.
1400 73rd Ave. NE
Minneapolis, MN 55432
U.S.A.

Phone: 1-763-574-5000
USA Toll-free: 1-877-769-7669
Fax: 1-763-574-5298
<http://homegenerators.cummins.com>

Bulletin NASB-6018-EN Printed in U.S.A. 1/18
©2018 Cummins Inc.



Extended Warranty Program

North America



Application	Models	Factory Standard Base Coverage	Extended Coverage	Level of Coverage			
				Parts Only	Parts + Labor	Parts + Labor + Travel	
Residential Standby	GGMA, GGMC, GGPC, GGHE, GGHF, GGHG, GGHH, GGHJ	2 years / 2000 hours Parts, Labor & Travel	5 years / 2000 hours	✓		✓	
	With Grid:GSBA, GSBB, GSBC (Canada Model)	5 years / 2000 hours Years 0-2: Parts, Labor & Travel Years 3-5: Parts Only	5 years / 2000 hours			✓	
	Off Grid: GSBA	1 year / 1000 hours Parts, Labor & Travel					
	C13N6H, C17N6H, C20N6H, C20N6HC	5 years / 2000 hours Years 0-2: Parts, Labor & Travel Years 3-5: Parts Only	5 years / 2000 hours			✓	
			7 years / 2000 hours			✓	
			10 years / 2000 hours			✓	
	C20 N6, C22 N6, C25 N6, C36 N6, C40 N6, C45N6, C50 N6, C60 N6, C70 N6, C80 N6, C100 N6, C30 N6H, C36 N6H, C40 N6H, C45 N6H, C50 N6H, C60 N6H	2 years / 1000 hours or 2 years / unlimited hours Parts, Labor & Travel	5 years / 2000 hours			✓	
			7 years / 2000 hours			✓	
			10 years / 2000 hours			✓	
	Light Commercial	DSKBA, DSFAA, DSFAD, DSFAE, DSGAA	2 years / 1000 hours Parts, Labor & Travel	3 years / 1500 hours	✓	✓	✓
4 years / 2000 hours				✓	✓	✓	
5 years / 2500 hours				✓	✓	✓	
6 years / 3000 hours				✓	✓	✓	
7 years / 3500 hours				✓	✓	✓	
8 years / 4000 hours				✓	✓	✓	
9 years / 4500 hours				✓	✓	✓	
10 years / 5000 hours				✓	✓	✓	
C10 D6, C15 D6, C20 D6, C25 D6, C30 D6, C35 D6, C40 D6, C50 D6, C60 D6C50D6C, C60D6C, C80D6C, C100D6C, C125D6C		2 years / 1000 hours Parts, Labor & Travel	3 years / 1500 hours	✓	✓	✓	
			4 years / 2000 hours	✓	✓	✓	
			5 years / 2500 hours	✓	✓	✓	
Light Commercial		Configurable Models:C20 N6, C22 N6, C25 N6, C30 N6, C36 N6, C40 N6, C30 N6H, C36 N6H, C40 N6H, C45 N6H, C50 N6H, C60 N6HC45 N6, C50 N6, C60 N6, C70 N6, C80 N6, C100 N6	2 years / 1000 hours Parts, Labor & Travel	3 years / 1500 hours	✓	✓	✓
				4 years / 2000 hours	✓	✓	✓
				5 years / 2500 hours	✓	✓	✓
	Preconfigured Models: C20 N6, C22 N6, C25 N6, C30 N6, C36 N6, C40 N6, C30 N6H, C36 N6H, C40 N6H, C45 N6H, C50 N6H, C60 N6HC50 N6, C60 N6, C80 N6, C100 N6	2 years / unlimited hours Parts, Labor & Travel	EPA-SE 3 years	✓	✓	✓	
			EPA-SE 4 years	✓	✓	✓	
			EPA-SE 5 years	✓	✓	✓	
ATS	RSS, RA	2 years Parts, Labor & Travel	5 years	✓		✓	
			7 years	✓		✓	
			10 years	✓		✓	